## Product data sheet

Specifications



# Safety switch, heavy duty, fusible, 200A, 3 wire, 3 pole, 150hp, 600VAC/DC, NEMA 1

H364

#### (Discontinued on: Jan 31, 2024

① Discontinued

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product	Single Throw Safety Switch				
Duty Rating	Heavy duty				
Device Application	Heavy application				
Disconnect Type	Fusible disconnect				
Factory Installed Neutral	None				
Phase	3 phase				
Number Of Poles	3				
Current Rating	200 A				
Voltage Rating	600 V AC/DC				
Enclosure Rating	NEMA 1 steel				
Motor Power Hp	50 hp at 480 V AC 50-60 Hz for 3 phase motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 60 hp at 600 V AC 50-60 Hz for 3 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC				

#### Complementary

Short-Circuit Current	10 kA for H or K 200 kA for R or J			
Fuse Type	H or K R or J			
Mounting Type	Surface			
Electrical Connection	Lugs			
Wiring Configuration	3-wire			
Wire Size	AWG 6250 kcmil copper or aluminium			
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)			
Depth	8.25 in (209.55 mm)			
Width	18.5 in (469.90 mm)			
Height	29 in (736.60 mm)			
Net Weight	54.50 lb(US) (24.72 kg)			

## Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

#### Ordering and shipping details

Category	US10DE100008		
Discount Schedule	0DE1		
Gtin	785901482314		
Returnability	Yes		
Country Of Origin	US		

## **Packing Units**

Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	8.30 in (21.082 cm)			
Package 1 Width	19.30 in (49.022 cm)			
Package 1 Length	30.80 in (78.232 cm)			
Package 1 Weight	44.80 lb(US) (20.321 kg)			
Unit Type Of Package 2	PAL			
Number Of Units In Package 2	15			
Package 2 Height	46.00 in (116.84 cm)			
Package 2 Width	40.00 in (101.6 cm)			
Package 2 Length	48.00 in (121.92 cm)			
Package 2 Weight	690.00 lb(US) (312.978 kg)			

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes
 Pvc Free

#### **Certifications & Standards**


Reach Regulation	REACh Declaration Compliant			
Eu Rohs Directive				
	EU RoHS Declaration			
China Rohs Regulation	China RoHS declaration			
	Pro-active China RoHS declaration (out of China RoHS legal scope)			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			


## Product data sheet

H364

#### **Dimensions Drawings**

#### Approximate Dimensions





KNOCKOUTS							
SYMBOL	CONDUIT SIZE		DIAMETER				
	IN	MM	IN	MM			
Α	.50	13	.88	22			
В	.75	19	1.13	29			
С	1.00	25	1.38	35			
D	1.25	32	1.75	45			
E	1.50	38	2.00	51			
F	2.00	51	2.50	64			
G	2.50	64	3.00	76			
н	3.00	76	3.50	89			