

Product data sheet

Characteristics

HDF36000F15

PowerPact H Circuit Breaker, No Trip Unit, 150A, 2P, 600V, 14kA

Product availability : Stock - Normally stocked in distribution facility



Price* : 585.00 USD



Main

Product or component type	Frame
Range of product	PowerPact H

Complementary

Line Rated Current	70...150 A
Number of Poles	3P
Interrupt Rating	18 kA at 480 V AC 25 kA at 240 V AC 14 kA at 600 V AC
System Voltage	250 V DC 600 V AC
Mounting mode	Unit mount
Electrical connection	Busbar connection load Busbar connection line
Height	6.4 in
Width	4.12 in
Depth	4.36 in
Tightening torque	5 N.m for 2.5...95 mm ² (AWG 14...AWG 3/0)

Environment

Product certifications	IEC CE CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01110 - HD,JD UNIT MT BREAKER/SWITCH
Discount Schedule	DE2
GTIN	00785901677550
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3700000000000001
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------