





PowerPact

PowerPact H

Circuit breaker, PowerPacT H, 35A, 3 pole, 600VAC, 50kA, I-Line, thermal magnetic, 80%, CBA

HLA360356

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,993.00 USD

Main Range

Product Name

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

AWG 14...AWG 3/0 aluminium/copper terminal

Switched off (OFF) 1 trip indicator green)

750 V IEC 60947-2

Yes IEC 60947-2

Category A

[Ui] Rated Insulation Voltage

Suitability For Isolation

Utilisation Category

Awg Gauge

Local Signalling

Mounting Mode	I-Line bracket)
Mounting Support	Bracket
Electrical Connection	I-Line connection, line Lugs, load
Terminal Identifier	AL150HD
Mounting Height	4.5 in (114.30 mm)
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 10) 123.91 lbf.in (14 N.m) 0.020.15 in² (1095 mm²) (AWG 8AWG 3/0)
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)
Power Wire Stripping Length	0.63 in (16 mm)
Color	Black
Height	6.42 in (163 mm)
Width	4.09 in (104 mm)
Depth	3.39 in (86 mm)
Net Weight	4.85 lb(US) (2.2 kg)
Quantity Per Set	1
Phase Connection	CBA
Communication Interface	Modbus Ethernet
Circuit Breaker Application	HACR rated

Environment

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category	US10DE201122
Discount Schedule	0DE2
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.38 in (13.653 cm)
Package 1 Width	8.13 in (20.638 cm)
Package 1 Length	14.63 in (37.148 cm)
Package 1 Weight	4.00 lb(US) (1.814 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov