

HLL36150M38X

PowerPact H Circuit Breaker, Motor Protector, 150A, 3P, 600V, 50kA

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,057.00 USD



Main

Product or component type	Motor Circuit Protector
Range of product	PowerPact H
Trip Unit Type	Electronic
Breaking capacity code	L

Complementary

Line Rated Current	150 A
Number of Poles	3P
Interrupt Rating	125 kA at 240 V AC 100 kA at 480 V AC 50 kA at 600 V AC
System Voltage	600 V AC
Continuous current rating	80 %
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
Wire Gauge	AWG 14...AWG 3/0 (aluminium/copper)
[I _{th}] conventional free air thermal current	14...25 A
Height	6.4 in
Width	4.12 in
Depth	4.36 in
Tightening torque	5 N.m for 2.5...95 mm ² (AWG 14...AWG 3/0)

Environment

Product certifications	CSA CE
------------------------	-----------

UL listed
IEC

Ambient air temperature for operation 104 °F (40 °C)

Ordering and shipping details

Category	01107 - H/J ELEC TRIP UNIT MOUNT BREAKER/SW
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW) Compliant

 [Schneider Electric declaration of conformity](#)

California proposition 65 WARNING: This product can expose you to chemicals including:

----- Substance 1 DINP, which is known to the State of California to cause cancer, and

----- Substance 2 DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.

----- More information For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period 18 months