

Product data sheet

Specifications

SQUARE D



TRFMR DRY TYPE 45KVA 240-208ZZ120,30D

HM45T254NCU

! Discontinued on: Nov 1, 2022

! Discontinued

Main

Product	Harmonic Mitigating Transformer
Enclosure Code	18D
Enclosure Type	NEMA 2
Insulation Temperature	392 °F (200 °C)
Phase	3 phase
Primary Voltage	240 V delta
Power Rating	45 kVA
Secondary Voltage	208Y/120 V
Temperature Rise	130° C
Winding Material	Copper
Phase Shift	+30°

Ordering and shipping details

Category	16274-HARMONIC MITIGATING LV XFMR
Discount Schedule	PE2E
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	375.00 lb(US) (170.097 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.