

# Product data sheet

Specifications

SQUARE D



## TRFMR DRY TYPE 75KVA 480-208ZZ120,30D

HM75T255NCU

⚠ Discontinued on: Nov 1, 2022

⚠ Discontinued

### Main

Product	Harmonic Mitigating Transformer
Enclosure Code	20D
Enclosure Type	NEMA 2
Insulation Temperature	392 °F (200 °C)
Phase	3 phase
Primary Voltage	480 V delta
Power Rating	75 kVA
Secondary Voltage	208Y/120 V
Full Capacity Taps	3 5 % 1+ 3-
Temperature Rise	130° C
Winding Material	Copper
Phase Shift	+30°

### Ordering and shipping details

Category	16274-HARMONIC MITIGATING LV XFMR
Discount Schedule	PE2E
Returnability	No

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	525.00 lb(US) (238.136 kg)

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**Environmental Disclosure**

[Product Environmental Profile](#)