

# Product data sheet

## Characteristics

# HMIBSU0ND1001

S-Box PC Universal HMIBSU No storage drive, DC, 1 slot

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\* : 1405.00 USD



### Main

Range of product	Magelis iPC
Product or component type	PC BOX
Device short name	S-BOX PC Universal
Processor name	Atom N2600 dual core 1.6 GHz
Free slots	1 Internal SATA SSD 1 CFast

### Complementary

Range compatibility	IDisplay
Memory description	Internal 4 GB RAM DDR3
Number of slots	1 mini PCI Express full-size
Display resolution	1920 x 1200 pixels
Watchdog timer	1...255 ms
Type of cooling	Fanless
Integrated connection type	COM1 serial link with 2 male SUB-D 9 RS232 VGA with 1 Ethernet with 3, transmission rate: 10/100/1000 Mbps USB 2.0 port with 5 COM1 serial link with 4 male SUB-D 9 RS232/422/485 Audio output with 1 HDMI with 1
[Us] rated supply voltage	24 V DC power supply
Supply voltage limits	12...24 V
Line Rated Current	1.5 A
Power consumption in W	16 W
Input/Output number	8 digital configurable by software
Depth	5.24 in (133 mm)
Height	2.69 in (68.4 mm)
Width	10.41 in (264.5 mm)
Product weight	5.51 lb(US) (2.5 kg)
Main type	Universal

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Product certifications	CCC CULus GOST
Standards	CSA 22-2 No 60950-1-07 EN 55011 class A group 1 EN 61000-6-4 FCC Part 15 UL 60950-1 EN 61131-2 ed. 3
Quality labels	CE
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive
IP degree of protection	IP40 conforming to IEC 60529
Electromagnetic compatibility	Conducted and radiated emissions class A EN 55022 Immunity to high frequency interference IEC 61000-4 Disturbing field emission class A EN 55011
Ambient air temperature for storage	-40...185 °F (-40...85 °C) conforming to IEC 60068-2-14 -40...185 °F (-40...85 °C) conforming to IEC 60068-2-2
Relative humidity	10...85 % conforming to EN/IEC 60068-2-30
Ambient air temperature for operation	32...122 °F (0...50 °C) conforming to EN/IEC 60068-2-2
Operating altitude	2000 conforming to IEC 60664-1
Vibration resistance	1.75 mm 2...9 Hz conforming to IEC 60068-2-6 0.5 gn 9...200 Hz conforming to IEC 60068-2-6
Shock resistance	50 gn 11 ms conforming to IEC 60068-2-27

## Ordering and shipping details

Category	22575 - MAGELIS MC3
Discount Schedule	MC3
GTIN	00785901312772
Nbr. of units in pkg.	1
Package weight(Lbs)	7.270000000000005
Returnability	N
Country of origin	CN

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1526 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------