## **Product data sheet**

Specification





multi touch screen, Harmony iPC, S panel PC optimized, 32GB back side CFast card, 15inch wide display

HMIPSOC752D1W01

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 3,544.58 USD

#### Main

Range Of Product	Harmony iPC					
Product Or Component Type	Multi-touch screen					
Processor Name	Intel Atom E3827 dual core at 1.75 GHz					
Chipset Type	Intel Atom SoC					
Free Slots	1 CFast					
Display Size	15.6 inch					
Display Colour	16777216 colors					
Luminance	27.87 fc (300 cd/m²)					
Pixel Resolution	4096 x 4096					
Video Controller Type	Intel HD Graphics					
Operating System	WES 7 Premium SP1 64-bitmulti-language					
Software Package	EcoStruxture secure connect advisor annual subscription cyber security license not included EcoStruxure Operator Terminal Expert run time HMI license not included EcoStruxure Machine SCADA Expert run time HMI/SCADA on configured offer only EcoStruxure augmented operator advisor server augmented operator license not included					

#### Complementary

Number Of Points	5					
Terminal Type	Touchscreen display					
Memory Type	4 GB RAM DDR3 internal					
Data Storage Equipment	32 GB back side CFast card					
Aspect Ratio	16:9					
Display Type	LED Colour TFT LCD					
Display Resolution	1366 x 768 pixels WXGA					
Backlight Lifespan	50000 hours					
View Angle Horizontal X Vertical	150 x 140°					
Touch Panel	Projected capacitive technology (PCT)					
Type Of Cooling	Passive Fanless					

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Watchdog Timer	1255 ms					
[Us] Rated Supply Voltage	24 V DC +/- 20 % 100240 V AC with additional adaptor HMIYPSOMAC1					
Line Rated Current	1.7 A					
Mechanical Robustness	Hardness anti-scratch 7H					
Local Signalling	buzzer for on LED (green) for stand-by LED (orange)					
Function Available	Operate with water on screen					
Width	16.52 in (419.7 mm)					
Height	10.59 in (269 mm)					
Depth	2.44 in (61.9 mm)					
Cut-Out Dimensions	412.4 (+/- 0.7) x 261.7 (+/- 0.4)					
Net Weight	8.60 lb(US) (3.9 kg)					
Display Size	15" wide multi-touch					
Main Type	Optimised					

### **Environment**

RCM AS/NZS C-tick CE CCC EAC				
C-tick CE CCC EAC				
CE CCC EAC				
CCC EAC				
EAC				
ECC Part 15 along A				
FCC Part 15 class A				
IEC 61000-6-4				
UL 60950				
IEC 61000-6-2				
IEC 60950				
CISPR 11				
CSA C22.2 No. 60950				
2006/95/EC - low voltage directive				
2004/108/EC - electromagnetic compatibility				
2				
32131 °F (055 °C) SSD				
32131 °F (055 °C) Cfast card				
32113 °F (045 °C) HDD				
32113 °F (045 °C) Mini PCIe				
-4140 °F (-2060 °C)				
1095 % non-condensing				
2000				
1 gn 5500 Hz)HDD				
2 gn 5500 Hz)SSD				
2 gn 5500 Hz)Cfast card				

# Ordering and shipping details

Category	US10MC322575		
Discount Schedule	0MC3		
Gtin	3606480853418		
Returnability	No		

Country Of Origin US

### **Packing Units**

_				
Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	2.44 in (6.2 cm)			
Package 1 Width	10.59 in (26.9 cm)			
Package 1 Length	16.54 in (42.0 cm)			
Package 1 Weight	8.82 lb(US) (4.0 kg)			
Unit Type Of Package 2	P12			
Number Of Units In Package 2	6			
Package 2 Height	31.50 in (80 cm)			
Package 2 Width	41.34 in (105 cm)			
Package 2 Length	49.21 in (125 cm)			
Package 2 Weight	108.03 lb(US) (49 kg)			

### Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


✓ Reach Free Of Svhc
 ✓ Mercury Free
 ✓ Rohs Exemption Information


#### **Certifications & Standards**


Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	End of Life Information				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

#### **Dimensions Drawings**

#### **Dimensions**








- (1) Front view
- (2) Right view

# Product data sheet HMIPSOC752D1W01

- (3) Back view
- (4) Bottom view

#### Mounting and Clearance

#### **Spacing Requirements**




- 1: Air out
- 2: Air in

#### **Mounting Orientation**



#### **Panel Cut Dimensions**



Α	A B		С		R		
mm	in.	mm	in.	mm	in.	mm	in.
412.4	16.24	261.7	10.30	26	0.080.23	5	0.20