# **Product data sheet**

Specifications





## Multi touch screen, Harmony iPC, S Panel PC Performance HDD W15 DC Windows 7

HMIPSPH752D1701

! Discontinued on: Sep 30, 2023

! To be end-of-service on: Mar 31, 2026

① Discontinued - Service only

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony iPC				
Product Or Component Type	Multi-touch screen				
Processor Name	Intel Core i3 4010U at 1.7 GHz				
Chipset Type	Intel QM87				
Free Slots	1 Internal SATA HDD/SSD 1 CFast				
Display Size	15.6 inch				
Display Colour	16777216 colors				
Luminance	27.87 fc (300 cd/m²)				
Pixel Resolution	4096 x 4096				
Video Controller Type	Intel HD Graphics 4400				
Operating System	Windows 7 64 bits Ultimate SP1				
Software Package	EcoStruxture secure connect advisor annual subscription cyber security license not included EcoStruxure Operator Terminal Expert run time HMI license not included EcoStruxure Machine SCADA Expert run time HMI/SCADA on configured offer only EcoStruxure augmented operator advisor server augmented operator license not included				

### Complementary

Number Of Points	5			
Terminal Type	Touchscreen display			
Memory Type	8 GB RAM DDR3 internal			
Data Storage Equipment	500 GB back side enterprise hard disk			
Aspect Ratio	16:9			
Display Type	Colour TFT LCD LED			
Display Resolution	1366 x 768 pixels WXGA			
Backlight Lifespan	50000 hours			
View Angle Horizontal X Vertical	150 x 140°			
Touch Panel	Projected capacitive technology (PCT)			

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Type Of Cooling	Fanless Passive				
Watchdog Timer	1255 ms				
Number Of Slots	1 mini PCI Express full-size				
[Us] Rated Supply Voltage	24 V DC +/- 20 % 100240 V AC with additional adaptor HMIYPSPMAC1				
Power Consumption In W	1860 W				
Mechanical Robustness	Hardness anti-scratch 7H				
Local Signalling	buzzer for on LED (green) for stand-by LED (orange)				
Function Available	Operate with water on screen				
Width	16.52 in (419.7 mm)				
Height	10.59 in (269 mm)				
Depth	2.23 in (56.7 mm)				
Cut-Out Dimensions	412.4 (+/- 0.7) x 261.7 (+/- 0.4)				
Net Weight	13.23 lb(US) (6 kg)				
Display Size	15" wide multi-touch				
Main Type	Performance				

### **Environment**

Ip Degree Of Protection	IP66 front panel:			
Product Certifications	CE			
	AS/NZS			
	CCC			
	C-tick			
	EAC			
	RCM			
Standards	FCC Part 15 class A			
	IEC 60950			
	IEC 61000-6-2			
	CSA C22.2 No. 60950			
	CISPR 11			
	UL 60950			
	IEC 61000-6-4			
Directives	2004/108/EC - electromagnetic compatibility			
	2006/95/EC - low voltage directive			
Pollution Degree	2			
Ambient Air Temperature For	32131 °F (055 °C) SSD			
Operation	32131 °F (055 °C) Cfast card			
	32113 °F (045 °C) HDD			
	32113 °F (045 °C) Mini PCIe			
Ambient Air Temperature For Storage	-4140 °F (-2060 °C)			
Relative Humidity	1095 % non-condensing			
Operating Altitude	2000			
Vibration Resistance	1 gn 5500 Hz)HDD			
	2 gn 5500 Hz)SSD			
	2 gn 5500 Hz)Cfast card			

# Ordering and shipping details

Category US10MC322575

Discount Schedule	0MC3		
Gtin	3606480928994		
Returnability	No		
Country Of Origin	US		

# **Packing Units**

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	20.67 in (52.5 cm)		
Package 1 Width	7.09 in (18.0 cm)		
Package 1 Length	27.76 in (70.5 cm)		
Package 1 Weight	17.64 lb(US) (8.0 kg)		

## Sustainability Green Premium™

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


✓ Reach Free Of Svhc
 ✓ Mercury Free
 ✓ Rohs Exemption Information

### **Certifications & Standards**

Reach Regulation	Pro-active compliance (Product out of EU RoHS legal scope)				
Eu Rohs Directive					
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	End of Life Information				
	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

### **Dimensions Drawings**


#### **Dimensions**



- (1) Front view
- (2) Right view

### Mounting and Clearance

### **Spacing Requirements**




- 1: Air out
- 2: Air in

### **Mounting Orientation**



### **Panel Cut Dimensions**



A B		С		R			
mm	in.	mm	in.	mm	in.	mm	in.
412.4	16.24	261.7	10.30	26	0.080.23	5	0.20