# Product data sheet

Specifications





(!) Discontinued

## Multi touch screen, Harmony iPC, S Panel PC Perf. SSD W19‮ DC Win 10 IoT Enterprise

HMIPSPS952D180L

- ! Discontinued on: Sep 15, 2023
- ! To be end-of-service on: Dec 31, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony iPC					
Product Or Component Type	Multi-touch screen					
Processor Name	Intel Core i3 4010U at 1.7 GHz					
Chipset Type	Intel QM87					
Free Slots	1 Internal SATA HDD/SSD 1 CFast					
Display Size	18.5 inch					
Display Colour	16777216 colors					
Luminance	27.87 fc (300 cd/m²)					
Pixel Resolution	4096 x 4096					
Video Controller Type	Intel HD Graphics 4400					
Operating System Windows 10 IoT Enterprise 64 bitmulti-language						
Software Package	EcoStruxture secure connect advisor annual subscription cyber security license not included EcoStruxure Operator Terminal Expert run time HMI license not included EcoStruxure Machine SCADA Expert run time HMI/SCADA on configured offer only EcoStruxure augmented operator advisor server augmented operator license not included Vijeo Citect DVD SCADA license not included					

## Complementary

Number Of Points	5			
Terminal Type	Touchscreen display			
Memory Type	8 GB RAM DDR3 internal			
Data Storage Equipment	256 GB back side SSD 1500000 h			
Aspect Ratio	16:9			
Display Type	Colour TFT LCD LED			
Display Resolution	1366 x 768 pixels WXGA			
Backlight Lifespan	50000 hours			
View Angle Horizontal X Vertical	150 x 140°			
Touch Panel	Projected capacitive technology (PCT)			

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Type Of Cooling	Passive			
	Fanless			
	r dilless			
Watchdog Timer	1255 ms			
Electrical Connection	Connector, connector type: SMA, 3 ways			
Number Of Slots	1 mini PCI Express full-size			
[Us] Rated Supply Voltage	24 V DC +/- 20 %			
	100240 V AC with additional adaptor HMIYPSPMAC1			
Power Consumption In W	1860 W			
rower consumption in w	1800 W			
Mechanical Robustness	Hardness anti-scratch 7H			
	Hardings and Soldon III			
Local Signalling	buzzer			
	for on LED (green)			
	for stand-by LED (orange)			
	ioi stand-by LED (orange)			
Function Available	Operate with water on screen			
<b>Width</b> 19.21 in (488 mm)				
Height	12.17 in (309 mm)			
Donth	0.00 :- (50.7)			
Depth	2.23 in (56.7 mm)			
Cut-Out Dimensions	479.3 (+/- 1) x 300.3 (+/- 0.7)			
	110.0 (11 1) 1000.0 (11 0.1)			
Net Weight	15.43 lb(US) (7 kg)			
Display Size	19" wide multi-touch			
Main Type	Performance			

### **Environment**

Ip Degree Of Protection	IP66 front panel:			
Product Certifications	CE			
	C-tick			
	CCC			
	EAC			
	RCM			
	AS/NZS			
Standards	UL 60950			
	CISPR 11			
	IEC 61000-6-4			
	IEC 61000-6-2			
	FCC Part 15 class A			
	CSA C22.2 No. 60950			
	IEC 60950			
Directives	2004/108/EC - electromagnetic compatibility			
	2006/95/EC - low voltage directive			
Pollution Degree	2			
Ambient Air Temperature For	32131 °F (055 °C) SSD			
Operation	32131 °F (055 °C) Cfast card			
	32113 °F (045 °C) HDD			
	32113 °F (045 °C) Mini PCle			
Ambient Air Temperature For Storage	-4140 °F (-2060 °C)			
Relative Humidity	1095 % non-condensing			
Operating Altitude	2000			
Vibration Resistance	1 gn 5500 Hz)HDD			
	2 gn 5500 Hz)SSD			
	2 gn 5500 Hz)Cfast card			

# Ordering and shipping details

Category	US10MC322575		
Discount Schedule	0MC3		
Gtin	3606480929069		
Returnability	No		
Country Of Origin	US		

# **Packing Units**

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	19.49 in (49.5 cm)		
Package 1 Width	6.30 in (16.0 cm)		
Package 1 Length	26.97 in (68.5 cm)		
Package 1 Weight	13.23 lb(US) (6.0 kg)		

## Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


<b>②</b>	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	End of Life Information				
	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

#### **Dimensions Drawings**


#### **Dimensions**



- (1) Front view
- (2) Right view

### Mounting and Clearance

### **Spacing Requirements**




- 1: Air out
- 2: Air in

### **Mounting Orientation**



Apr 19, 2024

### **Panel Cut Dimensions**



A		В		С		R	
mm	in.	mm	in.	mm	in.	mm	in.
479.3	18.87	300.3	11.82	26	0.080.23	5	0.20