

Product data sheet

Specifications



EcoStruxure Machine SCADA V8.1 for LineManag plus (Buildtime DVD), 4000 Tags

HMIVXLBT4KDV80

 **Discontinued on:** Jul 28, 2021

 **Discontinued**

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	EcoStruxure Machine Expert
Product Or Component Type	Software
Language	Multi-language
Format	Sticker DVD
Previous Software Version	V8.0 SP2

Complementary

Range Compatibility	Harmony GTU Harmony iPC
Software Designation	Line management
Type Of License	Design/operation (BT/RT)
Software Type	EcoStruxure machine SCADA Expert software
System Requirements	> 2 GB HDD storage device, > 2 GB primary memory > 2 GB HDD storage device Windows 8.1, > 2 GB primary memory > 2 GB HDD storage device Windows 10, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2008 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2012 R2, > 2 GB primary memory > 2 GB HDD storage device Windows Server 2016, > 2 GB primary memory Microsoft internet explorer 6 External audio and video files .NET Framework 3.5
Software Version	V8.1
Provided Equipment	User's documentation in electronic format
Document Type	Quick start-up guide Technical reference manual Training manual
Software Function	Database connection E-signature
Audio Video Coding Standard	MP3 MPEG AVI WAV MP4 MOV

Ordering and shipping details

Category	US10MC222574
Discount Schedule	0MC2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3606481171634
Returnability	No
Country Of Origin	JP

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	7.52 in (19.1 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	1.41 oz (40 g)