# **Product data sheet**

Specifications



Mini circuit breaker, Homeline, 15A, 1 pole, 120VAC, 10kA AIR, combo arc fault, pigtail neutral, plug in, UL

HOM115CAFI

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 267.00 USD

### Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Short Circuit Current Rating	10 kA
Number Of Spaces	1
Circuit Breaker Type	Combination ARC-fault
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	1 x AWG 14AWG 8 ( aluminium/copper )

### Complementary

Connections - Terminals	Pigtail neutral
Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in <sup>2</sup> (2.56 mm <sup>2</sup> ) (AWG 14AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

### Environment

Ambient Air Temperature For  $$104\ ^\circ F\ (40\ ^\circ C)$$  Operation

## Ordering and shipping details

Category	US1DE3D06301	
Discount Schedule	DE3D	
Gtin	785901439721	
Returnability	Yes	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country	Of	Origin	
---------	----	--------	--

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	5.50 in (13.97 cm)
Package 1 Weight	10.40 oz (294.835 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	38
Package 2 Height	3.90 in (9.906 cm)
Package 2 Width	13.90 in (35.306 cm)
Package 2 Length	20.80 in (52.832 cm)
Package 2 Weight	24.85 lb(US) (11.272 kg)

### **Contractual warranty**

Warranty

Lifetime

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov