





Mini circuit breaker, Homeline, 30A, 2 pole, 120/240VAC, 10kA AIR, ground fault class A, plug in, UL

HOM230GFI

Product availability: Stock - Normally stocked in distribution facility

Price\*: 413.00 USD

### Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	1 x AWG 12AWG 4 ( aluminium ) 1 x AWG 14AWG 6 ( copper )

## Complementary

Tightening Torque	40.71 lbf.in (4.6 N.m) 0.000.02 in² (2.510 mm²) (AWG 16AWG 14) 40.71 lbf.in (4.6 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

## **Environment**

Ambient Air Temperature For  $$104\ ^{\circ}\text{F}\ (40\ ^{\circ}\text{C})$$  Operation

## Ordering and shipping details

Category	US1DE3D00147
Discount Schedule	DE3D
Gtin	785901303237
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.40 in (8.636 cm)
Package 1 Width	2.40 in (6.096 cm)
Package 1 Length	5.40 in (13.716 cm)
Package 1 Weight	18.73 oz (531.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	33
Package 2 Height	5.40 in (13.716 cm)
Package 2 Width	13.90 in (35.306 cm)
Package 2 Length	20.90 in (53.086 cm)
Package 2 Weight	39.15 lb(US) (17.758 kg)

# **Contractual warranty**

Warranty Lifetime



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov