





# Load center, Homeline, 1 phase, 2 spaces, 4 circuits, 70A fixed main lugs, NEMA1, flush cover

HOM24L70F

Product availability: Stock - Normally stocked in distribution facility

Price\*: 59.00 USD

## Main

| Product Type                           | Load Center                             |  |
|--|---|--|
| Marketing Trade Name                   | Homeline                                |  |
| Load Center Type                       | Fixed Mains (lugs)                      |  |
| Rated Current                          | 70 A                                    |  |
| Number Of Spaces                       | 2                                       |  |
| Maximum Number Of Single Pole Circuits | 4                                       |  |
| Enclosure Rating                       | re Rating NEMA 1 indoor NEMA 3R outdoor |  |
| Cover Type                             | Flush cover                             |  |
| Electrical Connection                  | Lugs                                    |  |

## Complementary

| Max Short Circuit Current Rating  | 10 kA                                       |  |
|-----------------------------------|---|--|
| Maximum Number Of Tandem Breakers | 2   |  |
| Number Of Phases                  | 1 phase                                     |  |
| Voltage Rating                    | 120/240 V AC                                |  |
| Wire Size                         | AWG 12AWG 3 aluminium<br>AWG 14AWG 4 copper |  |
| Wiring Configuration              | 3-wire                                      |  |
| Busbar Material                   | Tin plated aluminium: busbar                |  |
| Enclosure Material                | Welded sheet steel                          |  |
| Surface Finish                    | Baked enamel Gray                           |  |
| Box Number                        | 2   |  |
| Height                            | 9.29 in (236 mm)                            |  |
| Width                             | 4.80 in (122 mm)                            |  |
| Depth                             | 3.19 in (81 mm)                             |  |

#### **Environment**

| Ambient Air Temperature For | 23 °F (-5 °C)         |  |
|-----------------------------|-----------------------|--|
| Operation                   | 104 °F (40 °C)        |  |
| Product Certifications      | UL listed file E-6294 |  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

| Category          | US1DE3C00149 |  |
|-------------------|--------------|--|
| Discount Schedule | DE3C         |  |
| Gtin              | 785901061151 |  |
| Returnability     | Yes          |  |
| Country Of Origin | MX           |  |

## **Packing Units**

| Unit Type Of Package 1       | PCE                        |  |
|------------------------------|----------------------------|--|
| Number Of Units In Package 1 | 1                          |  |
| Package 1 Height             | 4.02 in (10.2 cm)          |  |
| Package 1 Width              | 6.50 in (16.5 cm)          |  |
| Package 1 Length             | 11.10 in (28.2 cm)         |  |
| Package 1 Weight             | 3.68 lb(US) (1.67 kg)      |  |
| Unit Type Of Package 2       | PAL                        |  |
| Number Of Units In Package 2 | 222                        |  |
| Package 2 Height             | 40.00 in (101.6 cm)        |  |
| Package 2 Width              | 40.00 in (101.6 cm)        |  |
| Package 2 Length             | 48.00 in (121.92 cm)       |  |
| Package 2 Weight             | 842.58 lb(US) (382.188 kg) |  |

## **Contractual warranty**

Warranty Lifetime



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

| <b>②</b> | Toxic Heavy Metal Free     |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Compliant   |
|                           | EU RoHS Declaration   |
| China Rohs Regulation     | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |