





Mini circuit breaker, Homeline, 70A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM270

Product availability: Stock - Normally stocked in distribution

Price*: 123.00 USD

Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	70 A	
Certifications	UL Listed	
Voltage Rating	120/240 V AC	
Mounting Type	Plug-in	
Number Of Poles	2P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	2	
Circuit Breaker Type	pe Standard	
Ratings	HACR rated	
Electrical Connection	Box lugs	
Wire Size	e Size 1 x AWG 8AWG 2 (aluminium/copper)	

Complementary

Tightening Torque	40.71 lbf.in (4.6 N.m) (AWG 8AWG 2)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00146	
Discount Schedule	DE3D	
Gtin	785901065340	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.01 in (5.1 cm)	
Package 1 Width	3.23 in (8.2 cm)	
Package 1 Length	3.43 in (8.7 cm)	
Package 1 Weight	kage 1 Weight 11.68 oz (331.2 g)	
Unit Type Of Package 2	CAR	
Number Of Units In Package 2	40	
Package 2 Height	3.00 in (7.62 cm)	
Package 2 Width	14.60 in (37.084 cm)	
Package 2 Length	21.60 in (54.864 cm)	
Package 2 Weight	29.90 lb(US) (13.562 kg)	
Unit Type Of Package 3	PAL	
Number Of Units In Package 3	1800	
Package 3 Height	40.00 in (101.6 cm)	
Package 3 Width	40.00 in (101.6 cm)	
Package 3 Length	48.00 in (121.92 cm)	
Package 3 Weight	1353.00 lb(US) (613.71 kg)	

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations