

Product data sheet

Specifications

SQUARE D

Green Premium™



Load center accessory, Homeline, lug kit, main, 225A

HOML2225

Product availability: Stock - Normally stocked in distribution facility

Price*: 296.00 USD

Main

Product Type	Lug kit
Marketing Trade Name	Homeline

Complementary

Number Of Poles	2
Rated Current	225 A
Wire Size	AWG 4...300 kcmil
Height	5.39 in (136.91 mm)
Width	3.98 in (101.09 mm)
Depth	3.13 in (79.50 mm)
Tightening Torque	28 N.m, AWG 1...300 kcmil
Cable Cross Section	0.08...0.23 in ² (50...150 mm ²) - AWG 1...300 kcmil

Ordering and shipping details

Category	US1DE3C00150
Discount Schedule	DE3C
Gtin	785901852469
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.70 in (14.478 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	7.70 in (19.558 cm)
Package 1 Weight	2.75 lb(US) (1.247 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [No need of specific recycling operations](#)