

Product availability : Stock - Normally stocked in distribution facility



Price\* : 52.00 USD



### Main

Product	Miniature circuit-breaker
Range	Homeline
Line Rated Current	15 A
Certifications	UL listed
System Voltage	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 14...AWG 8 for 1 cable(s) (aluminium/copper)
Height	3.13 in
Width	1 in
Depth	2.98 in

### Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

### Ordering and shipping details

Category	00046 - HOM/T 15-30A 1P; 15-60A 2P
Discount Schedule	DE3D
GTIN	00785901065388
Nbr. of units in pkg.	10
Package weight(Lbs)	0.4500000000000001
Returnability	Y

---

Country of origin	MX
-------------------	----

---

**Offer Sustainability**

---

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

**Contractual warranty**

---

Warranty period	Lifetime
-----------------	----------

---