





Tandem circuit breaker, Homeline, 1 x 1 pole at 30A, 1 x 1 pole at 20A, 120/240VAC, 10kA AIR, plug in, UL

HOMT3020

Product availability: Stock - Normally stocked in distribution facility

Price\*: 52.00 USD

### Main

| Product                      | Miniature circuit-breaker            |
|------------------------------|--------------------------------------|
| Range                        | Homeline                             |
| Current Rating               | 20 A<br>30 A                         |
| Certifications               | UL Listed                            |
| Voltage Rating               | 120/240 V AC                         |
| Mounting Type                | Plug-in                              |
| Number Of Poles              | 1P                                   |
| Short Circuit Current Rating | 10 kA                                |
| Number Of Spaces             | 1                                    |
| Circuit Breaker Type         | Tandem                               |
| Ratings                      | HACR rated                           |
| Electrical Connection        | Box lugs                             |
| Wire Size                    | 1 x AWG 14AWG 8 ( aluminium/copper ) |

### Complementary

| Tightening Torque | 35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8) |
|-------------------|--|
| Height            | 3.13 in (79.50 mm)   |
| Width             | 1 in (25.40 mm)  |
| Depth             | 2.98 in (75.69 mm)   |

#### **Environment**

Ambient Air Temperature For 104 °F (40 °C)

## Ordering and shipping details

| Category          | US1DE3D00046 |
|-------------------|--------------|
| Discount Schedule | DE3D         |
| Gtin              | 785901706366 |
| Returnability     | Yes          |
| Country Of Origin | MX           |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

| Unit Type Of Package 1       | PCE                 |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1                   |
| Package 1 Height             | 3.20 in (8.128 cm)  |
| Package 1 Width              | 1.00 in (2.54 cm)   |
| Package 1 Length             | 3.00 in (7.62 cm)   |
| Package 1 Weight             | 6.88 oz (195.045 g) |

## **Contractual warranty**

Warranty Lifetime

Apr 24, 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

## **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |