





Safety switch, heavy duty, non fusible, 30A, 3 poles, 30hp, 600VAC/DC, NEMA 4, 4X, 5, 304 steel, interlock kit

HU361DSEI2

① Discontinued

! Discontinued on: Jun 23, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	ry Installed Neutral None	
Phase	3 phase	
Number Of Poles	or Of Poles 3	
Current Rating	30 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 4/4X/5 stainless steel 304	
Motor Power Hp	5 hp at 240 V AC 50-60 Hz for 1 phase motors 10 hp at 240 V AC 50-60 Hz for 3 phase motors 7.5 hp at 480 V AC 50-60 Hz for 1 phase motors 20 hp at 480 V AC 50-60 Hz for 3 phase motors 10 hp at 600 V AC 50-60 Hz for 1 phase motors 30 hp at 600 V AC 50-60 Hz for 3 phase motors 5 hp at 250 V DC 15 hp at 600 V DC	

Complementary

Mounting Type	Surface	
Wiring Configuration	3-wire	
Wire Size	AWG 12AWG 6 aluminium AWG 14AWG 6 copper	
Tightening Torque	45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)	
Depth	th 5.11 in (129.79 mm)	
Width	8.67 in (220.22 mm)	
eight 14.93 in (379.22 mm)		
Net Weight	t Weight 13.34 lb(US) (6.05 kg)	

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100160	
Discount Schedule	0DE1	
Gtin	785901077862	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.70 in (14.478 cm)
Package 1 Width	9.00 in (22.86 cm)
Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	13.00 lb(US) (5.897 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov