





Safety switch, heavy duty, non fusible, 30A, 4 pole, 30hp, 600VAC/DC, NEMA 4, 4X, 5, 304 steel

HU461DS

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,586.00 USD

Main

| Product | Single Throw Safety Switch | |
|---------------------------|--|--|
| Duty Rating | Heavy duty | |
| Device Application | Heavy application | |
| Disconnect Type | Non-fusible disconnect | |
| Factory Installed Neutral | None | |
| Phase | 3 phase | |
| Number Of Poles | 4 | |
| Current Rating | 30 A | |
| Voltage Rating | 600 V AC/DC | |
| Enclosure Rating | NEMA 4/4X/5 stainless steel 304 | |
| Motor Power Hp | 10 hp at 240 V AC 50-60 Hz for 2 phases motors 10 hp at 240 V AC 50-60 Hz for 3 phase motors 20 hp at 480 V AC 50-60 Hz for 2 phases motors 20 hp at 480 V AC 50-60 Hz for 3 phase motors 25 hp at 600 V AC 50-60 Hz for 2 phases motors 30 hp at 600 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC 15 hp at 600 V DC | |

Complementary

| Mounting Type | Surface | |
|-----------------------|---|--|
| Electrical Connection | Lugs | |
| Wiring Configuration | 4-wire | |
| Wire Size | AWG 12AWG 6 aluminium AWG 14AWG 6 copper | |
| Tightening Torque | 45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10) | |
| Depth | 6.97 in (177.04 mm) | |
| Width | 16.85 in (427.99 mm) | |
| Height | 20.82 in (528.83 mm) | |
| Net Weight | 30.86 lb(US) (14 kg) | |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| Category | US10DE100115 | |
|-------------------|--------------|--|
| Discount Schedule | 0DE1 | |
| Gtin | 785901507826 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| Unit Type Of Package 1 | PCE | |
|------------------------------|-------------------------|--|
| Number Of Units In Package 1 | 1 | |
| Package 1 Height | 25.00 in (63.5 cm) | |
| Package 1 Width | 7.13 in (18.11 cm) | |
| Package 1 Length | 16.50 in (41.91 cm) | |
| Package 1 Weight | 19.31 lb(US) (8.759 kg) | |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free | |
|----------|----------------------------|-----|
| ⊘ | Rohs Exemption Information | Yes |
| ⊘ | Pvc Free | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |