

# Product data sheet

Specifications



Switchgear, HVL, single, 600A, 4.76kV, 3 pole, 10 to 450E DIN/E current limit fuse, NEMA 1

HVL305DEG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 19,392.00 USD

## Main

Product	Switched fuse mechanism
Not Included	fuse to be ordered separately

## Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E 350 A E 500 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	4.76 kV
Basic Inulation Level	60 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Type Of Installation	Indoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	54.5 in (1384.30 mm)
Enclosure Height	90 in (2286.00 mm)

## Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	cUL UL Listed
------------------------	------------------

## Ordering and shipping details

Category	US1PE5A07942
Discount Schedule	PE5A
Gtin	3606486276334
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1200.00 lb(US) (544.311 kg)

## Contractual warranty

Warranty	18 months
----------	-----------