

Product data sheet

Specifications



Switchgear, HVL, single, 600A, 4.76kV, 3 pole, unfused, NEMA 3R

HVL305NW

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 21,524.00 USD

Main

Product	Switch mechanism
Included Accessory	Enclosure heater

Complementary

Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	4.76 kV
Basic Inulation Level	60 kV
Enclosure Rating	NEMA 3R
Electrical Connection	Lugs
Type Of Installation	Outdoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	60 in (1524.00 mm)
Enclosure Height	97 in (2463.80 mm)

Environment

Product Certifications	cUL UL Listed
------------------------	------------------

Ordering and shipping details

Category	US1PE5A07943
Discount Schedule	PE5A
Gtin	3606486276341
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1400.00 lb(US) (635.029 kg)
------------------	-----------------------------

Contractual warranty

Warranty	18 months
----------	-----------