

Product data sheet

Specifications



Switchgear, HVL, single, 600A, 15kV, 3 pole, 10E to 400E boric acid fuse, NEMA 1

HVL315BG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 39,975.00 USD

Main

Product	Switched fuse mechanism
Not Included	fuse to be ordered separately

Complementary

Protection Type	Fuse boric acid
Associated Fuse Rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	15 kV
Basic Inulation Level	90 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Type Of Installation	Indoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in (965.20 mm)
Enclosure Depth	54.5 in (1384.30 mm)
Enclosure Height	90 in (2286.00 mm)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	cUL UL Listed
------------------------	------------------

Ordering and shipping details

Category	US1PE5A07944
Discount Schedule	PE5A
Gtin	3606486276358
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	1200.00 lb(US) (544.311 kg)

Contractual warranty

Warranty	18 months
----------	-----------