

Product data sheet

Characteristics

HVL315BW

HVL Digest Switch 15KV NEMA 3R 10-400E Boric Acid Fuse

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 30,688.00 USD



Main

Product	Switched fuse mechanism
Included Accessory	Enclosure heater
Not Included	Fuse to be ordered separately

Complementary

Protection type	Fuse boric acid
Associated fuse rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number of Poles	3P
[Ur] highest voltage for equipment	15 kV
Basic Inulation Level	90 kV
Enclosure Rating	NEMA 3R
Electrical connection	Lugs

Type of installation	Outdoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in
Enclosure Depth	60 in
Enclosure Height	97 in

Environment

Product certifications	CUL UL listed
------------------------	------------------

Ordering and shipping details

Category	07945 - 15KV DIGEST HVL NEMA 3R
Discount Schedule	PE5A
GTIN	00785901741503
Nbr. of units in pkg.	1
Package weight(Lbs)	1400
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------