

Product data sheet

Characteristics

HVL315DEW1

HVL Digest Switch 15 KV NEMA 3R 10-100E DIN/E Current Limiting Fuse

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 23,978.00 USD



Main

Product	Switched fuse mechanism
Included Accessory	Enclosure heater
Not Included	Fuse to be ordered separately

Complementary

Protection type	Fuse current limiter
Associated fuse rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Frequency	50/60 Hz
Number of Poles	3P
[Ur] highest voltage for equipment	15 kV
Basic Inulation Level	90 kV
Enclosure Rating	NEMA 3R
Electrical connection	Lugs
Type of installation	Outdoor
Wire Gauge	AWG 2...600 kcmil aluminium/copper
Enclosure Width	38 in
Enclosure Depth	60 in

Enclosure Height	97 in
------------------	-------

Environment

Product certifications	UL listed CUL
------------------------	------------------

Ordering and shipping details

Category	07945 - 15KV DIGEST HVL NEMA 3R
Discount Schedule	PE5A
Nbr. of units in pkg.	1
Package weight(Lbs)	1200
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
