

# Product data sheet

Specifications

SQUARE D



Switchgear, HVLcc, fused, 4.76kV, 600A, 20.00in W, top entry, transformer on left

HVLCCA20405DGL

⚠ Discontinued on: May 19, 2023

⚠ Discontinued

Product availability: Stock - Normally stocked in distribution facility

## Main

Product	Switched fuse mechanism
Application	A
Not Included	fuse to be ordered separately
Device Application	Transformer left side

## Complementary

Protection Type	Fuse current limiter
Associated Fuse Rating	10 A E 15 A E 20 A E 25 A E 30 A E 40 A E 50 A E 65 A E 80 A E 100 A E 125 A E 150 A E 175 A E 200 A E 250 A E 300 A E 400 A E 350 A E 500 A E
Line Rated Current	600 A
Momentary Amperes Asymmetrical	40 kA
Full Load Current	300 A
Frequency	50/60 Hz
Number Of Poles	3P
Highest Voltage For Equipment (Um)	4.76 kV
Basic Inulation Level	60 kV
Enclosure Rating	NEMA 1
Electrical Connection	Lugs
Wire Gauge	AWG 2...350 kcmil 2 aluminium/copper
Service Entry	OH
Enclosure Width	20 in (508.00 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Enclosure Depth	37.25 in (946.15 mm)
Enclosure Height	90 in (2286.00 mm)

## Ordering and shipping details

Category	07948-DIGEST HVL/CC
Discount Schedule	PE5A
Gtin	3606486276938
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	530.00 lb(US) (240.404 kg)

## Contractual warranty

Warranty	18 months
----------	-----------