Product data sheet

Specification





integrated servo motor - 1.7 Nm - 6000 rpm - keyed shaft - with brake

ILM0702P11F0000

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 5,875.86 USD

Main

Range Of Product	PacDrive 3	
Product Or Component Type	Servo motor integrated drive	
Device Short Name	ILM	

Complementary

[Us] Rated Supply Voltage	250700 V
Continuous Stall Current	2.5 A
Continuous Stall Torque	15.05 lbf.in (1.7 N.m)
Peak Stall Torque	67.27 lbf.in (7.6 N.m)
Nominal Output Power	720 W
Nominal Torque	10.18 lbf.in (1.15 N.m)
Nominal Speed	6000 rpm
Maximum Current Irms	11.8 A
Line Rated Current	1.5 A
Shaft End	Keyed
Second Shaft	Without second shaft end
Shaft Diameter	0.43 in (11 mm)
Shaft Length	0.91 in (23 mm)
Key Width	0.71 in (18 mm)
Feedback Type	Absolute single turn SinCos Hiperface
Speed Feedback Resolution	128 periods
Holding Brake	With
Holding Torque	26.55 lbf.in (3 N.m) holding brake
Mounting Support	International standard flange
Motor Flange Size	2.76 in (70 mm)
Torque Constant	0.76 N.m/A 248 °F (120 °C)
Back Emf Constant	48 V/krpm 68 °F (20 °C)
Number Of Motor Poles	6
Rotor Inertia	0.51 kg.cm²

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Stator Resistance	4.2 Ohm 68 °F (20 °C) Ph/Ph 2.92 Ohm 248 °F (120 °C) Ph/N
Stator Inductance	19 mH 68 °F (20 °C) Ph/Ph 9.5 mH 248 °F (120 °C) Ph/N
Maximum Radial Force Fr	710 N 1000 rpm 560 N 2000 rpm 490 N 3000 rpm 450 N 4000 rpm 410 N 5000 rpm 390 N 6000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	9.92 in (252 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)
Net Weight	8.16 lb(US) (3.7 kg)

Environment

Ip Degree Of Protection IP54

Ordering and shipping details

Category	US1PC5218351
Discount Schedule	PC52
Gtin	3606485293806
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	14.02 in (35.6 cm)
Package 1 Weight	9.44 lb(US) (4.28 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov