Product data sheet

Specifications





integrated servo motor - 8.5 Nm - 1500 rpm - with brake - IP65

ILM1401M21F0000

- ! Discontinued on: Sep 30, 2023
- ! To be end-of-service on: Mar 31, 2025

① Discontinued - Service only

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	PacDrive 3	
Product Or Component Type	Servo motor integrated drive	
Device Short Name	ILM	

Complementary

[Us] Rated Supply Voltage	250700 V
Continuous Stall Current	3.2 A
Continuous Stall Torque	75.23 lbf.in (8.5 N.m)
Peak Stall Torque	238.97 lbf.in (27 N.m)
Nominal Output Power	1300 W
Nominal Torque	73.46 lbf.in (8.3 N.m)
Nominal Speed	1500 rpm
Maximum Current Irms	14.6 A
Line Rated Current	3.15 A
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	0.94 in (24 mm)
Shaft Length	1.97 in (50 mm)
Key Width	1.57 in (40 mm)
Feedback Type	Absolute single turn SinCos Hiperface
Speed Feedback Resolution	128 periods
Holding Brake	With
Holding Torque	159.31 lbf.in (18 N.m) holding brake
Mounting Support	International standard flange
Motor Flange Size	5.51 in (140 mm)
Torque Constant	2.65 N.m/A 248 °F (120 °C)
Back Emf Constant	175 V/krpm 68 °F (20 °C)
Number Of Motor Poles	10
Rotor Inertia	7.41 kg.cm²

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Stator Resistance	4.58 Ohm 68 °F (20 °C) Ph/Ph 3.18 Ohm 248 °F (120 °C) Ph/N	
Stator Inductance	50 mH 68 °F (20 °C) Ph/Ph 25 mH 248 °F (120 °C) Ph/N	
Maximum Radial Force Fr	2210 N 1000 rpm 1760 N 2000 rpm	
Maximum Axial Force Fa	0.2 x Fr	
Type Of Cooling	Natural convection	
Length	11.50 in (292 mm)	
Number Of Motor Stacks	1	
Centring Collar Diameter	5.12 in (130 mm)	
Centring Collar Depth	0.14 in (3.5 mm)	
Number Of Mounting Holes	4	
Mounting Holes Diameter	0.43 in (11 mm)	
Circle Diameter Of The Mounting Holes	6.50 in (165 mm)	
Net Weight	30.42 lb(US) (13.8 kg)	

Environment

Ip Degree Of Protection IP65

Ordering and shipping details

Category	US1PC5218351
Discount Schedule	PC52
Gtin	3606485294643
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.24 in (26.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	23.23 in (59.0 cm)
Package 1 Weight	42.62 lb(US) (19.33 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov