Product data sheet

Specifications





integrated servo motor- 12.5 Nm-2000 rpm- keyed shaft-multiturnwith brake-IP65

ILM1402P32F0000

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 6,219.21 USD

Main

Range Of Product	PacDrive 3
Product Or Component Type	Servo motor integrated drive
Device Short Name	ILM
Complementary	
[Us] Rated Supply Voltage	250700 V
Continuous Stall Current	4.8 A
Continuous Stall Torque	110.63 lbf.in (12.5 N.m)
Peak Stall Torque	486.79 lbf.in (55 N.m)
Nominal Output Power	1910 W
Nominal Torque	80.54 lbf.in (9.1 N.m)
Nominal Speed	2000 rpm
Maximum Current Irms	24 A
Line Rated Current	3.7 A
Shaft End	Keyed
Second Shaft	Without second shaft end
Shaft Diameter	0.94 in (24 mm)
Shaft Length	1.97 in (50 mm)
Key Width	1.57 in (40 mm)
Feedback Type	Absolute multiturn SinCos Hiperface
Speed Feedback Resolution	128 periods
Holding Brake	With
Holding Torque	203.57 lbf.in (23 N.m) holding brake
Mounting Support	International standard flange
Motor Flange Size	5.51 in (140 mm)
Torque Constant	2.6 N.m/A 248 °F (120 °C)
Back Emf Constant	173 V/krpm 68 °F (20 °C)
Number Of Motor Poles	10
Rotor Inertia	12.68 kg.cm ²

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Stator Resistance	1.9 Ohm 68 °F (20 °C) Ph/Ph 1.32 Ohm 248 °F (120 °C) Ph/N
Stator Inductance	22 mH 68 °F (20 °C) Ph/Ph 11 mH 248 °F (120 °C) Ph/N
Maximum Radial Force Fr	2430 N 1000 rpm 1930 N 2000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	13.66 in (347 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	5.12 in (130 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.43 in (11 mm)
Circle Diameter Of The Mounting Holes	6.50 in (165 mm)
Net Weight	40.79 lb(US) (18.5 kg)

Environment

Ip Degree Of Protection

IP65

Ordering and shipping details

Category	US1PC5218351	
Discount Schedule	PC52	
Gtin	3606485295022	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.87 in (20.0 cm)
Package 1 Width	10.24 in (26.0 cm)
Package 1 Length	23.23 in (59.0 cm)
Package 1 Weight	56.28 lb(US) (25.53 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov