



Thorsman TET - grommet - grey - ISO M16 - diameter 5 to 7

IMT36180

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2.24 USD

Main

Product Range	Thorsman TET
Product Type	Grommet
Colour	Grey
Quantity Per Package	Set of 50

Complementary

Material	EPDM
Iso Thread	M16
Cable Outer Diameter	0.200.28 in (57 mm)
Drilling Diameter	0.63 in (16 mm)
Height	0.79 in (20 mm)
Width	0.79 in (20 mm)
Length	0.98 in (25 mm)

Environment

Ip-Class IP67

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480163791	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.71 in (1.8 cm)
Package 1 Width	0.79 in (2.0 cm)
Package 1 Length	0.79 in (2.0 cm)
Package 1 Weight	0.12 oz (3.5 g)
Unit Type Of Package 2	BB1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 2	50
Package 2 Height	1.57 in (4.0 cm)
Package 2 Width	2.95 in (7.5 cm)
Package 2 Length	5.12 in (13.0 cm)
Package 2 Weight	6.19 oz (175.5 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations