

# Product data sheet

## Characteristics

# IMT36182

Thorsman TET - grommet - grey - ISO M25 - diameter 10 to 14

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 4.40 USD



### Main

Product range	Thorsman TET
Product type	Grommet
Colour	Grey
Quantity per package	Set of 50

### Complementary

Material	EPDM
ISO thread	M25
Cable outer diameter	0.39...0.55 in (10...14 mm)
Drilling diameter	25.3 mm

### Environment

IP-Class	IP67
----------	------

### Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	003606480163814
Nbr. of units in pkg.	50
Package weight(Lbs)	2.2000000000000002
Returnability	N
Country of origin	FR

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 1838 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------