

Product data sheet

Specifications



Thorsman TET - grommet - grey - ISO M32 - diameter 14 to 20

IMT36183

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8.92 USD

Main

Product Range	Thorsman TET
Product Type	Grommet
Colour	Grey
Quantity Per Package	Set of 50

Complementary

Material	EPDM
Iso Thread	M32
Cable Outer Diameter	0.55...0.79 in (14...20 mm)
Drilling Diameter	1.28 in (32.4 mm)
Height	1.18 in (30 mm)
Width	1.89 in (48 mm)
Length	1.89 in (48 mm)

Environment

Ip-Class	IP67
----------	------

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480163821
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	1.50 in (3.8 cm)
Package 1 Length	1.50 in (3.8 cm)
Package 1 Weight	0.42 oz (12.0 g)
Unit Type Of Package 2	BB1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	50
Package 2 Height	9.84 in (25.0 cm)
Package 2 Width	6.30 in (16.0 cm)
Package 2 Length	2.76 in (7.0 cm)
Package 2 Weight	22.05 oz (625.0 g)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	850
Package 3 Height	15.75 in (40.0 cm)
Package 3 Width	12.60 in (32.0 cm)
Package 3 Length	11.81 in (30.0 cm)
Package 3 Weight	24.43 lb(US) (11.082 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)