





Circuit breaker enclosure, PowerPacT H/J, 15A to 250A, NEMA 3R, 14.47in W x 31.05in H x 6.28in D

J250R

Product availability: Stock - Normally stocked in distribution facility

Price\*: 840.00 USD

### Main

Breaker Compatibility

Circuit breaker H-Frame 15...250 A

Circuit breaker J-Frame 15...250 A

### **Complementary**

Height	31.05 in (788.67 mm)
Width	14.47 in (367.54 mm)
Depth	6.28 in (159.51 mm)

#### **Environmental**

Nema Degree Of Protection NEMA 3R

# Ordering and shipping details

Category	JS10DE100030				
Discount Schedule	0DE1				
Gtin	785901607861				
Returnability	Yes				
Country Of Origin	MX				

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.50 in (21.59 cm)
Package 1 Width	15.10 in (38.354 cm)
Package 1 Length	32.40 in (82.296 cm)
Package 1 Weight	33.96 lb(US) (15.405 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	12
Package 2 Height	39.00 in (99.06 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Weight

441.00 lb(US) (200.034 kg)

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


<b>Ø</b>	Toxic Heavy Metal Free
	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>Ø</b>	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


#### **Dimensions Drawings**

#### **Approximate Dimensions**



#### Connections and Schema

## **Connections and Wiring Diagrams**



▲H150R AND J250R NEMA TYPE 3R

CIRCUIT BREAKER TERMINAL LUG DATA									
CIRCUIT BREAKER CATALOG NO.		CONDUCTORS PER PHASE	WIRE (AWG/	TYPE					
PREFIX	RATING	PER PHASE	MAX	MIN					
HD, HG HJ, HL, HR	15-150	1	#3/0	#14	AL/CU				
JD, JG JJ, JL, JR	150-175	1	#4/0	#4	AL/CU				
	200-250	1	350	#3/0	AL/CU				

FIELD INSTALLABLE SOLID NEUTRAL ASSEMBLIES AND GROUND KIT									
CATALOG NUMBER	MAXIMUM AMPERE	NUMBER OF TERMINALS	CONDUCTORS		SIZE KCMIL)	TYPE			
NUMBER	RATING	TERMINALS	TERMINAL	MAX	MIN				
SN100FA	100A	2	1	#1/0	#14	CU			
SNIOOFA	TOUR		'	#1/0	#12	AL			
SN400LA 250A		2	1 OR 2	#600 #250	#1 #1	AL OR CU AL OR CU			
		2	1	#300	#4	AL OR CU			
PK0GTJ250	250A	2	1	#300	#6	AL OR CU			
PK0GTH150	150A	2	1	#2	#14	AL OR CU			

FOR 200% NEUTRALS USE SN400LA (AMP RANGE 100 TO 250, CU WIRE ONLY).

FIELD INSTALLABLE CIRCUIT BREAKER DATA										
CIRCUIT BREAKER CATALOG NO	WIRING DIAG	AMPERE RATING	UL LISTED INTERRUPTING RATING RMS SYMMETRICAL AMPERES							
			AC VOLTAGE					DC VOLTAGE		
PREFIX			240	480Y/277	480	600Y/347	600	125	250	500
▲HD JD	A,B A,B	15-150 150-250	25K 25K	18K 18K	18K 18K	14K 14K	14K 14K	20K 20K	20K 20K	_
▲HG JG	A,B A,B	15-150 150-250	65K 65K	35K 35K	35K 35K	18K 18K	18K 18K	20K 20K	20K 20K	_
JJ HJ	A,B A,B	15-150 150-250	100K	65K 65K	65K 65K	25K 25K	25K 25K	20K 20K	20K 20K	_
HL JL	A,B A,B	15-150 150-250	125K 125K	65K 65K	65K 65K	25K 25K	25K 25K	20K 20K	20K 20K	-
HR JR	A,B A,B	15-150 150-250	125K 125K	65K 65K	65K 65K	25K 25K	25K 25K	20K 20K	20K 20K	_

▲H150R SUITABLE ONLY FOR 2 POLE HD OR HG BREAKERS.