

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 5985.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact J
Trip unit technology	Thermal-magnetic
Breaking capacity code	L

Complementary

Line Rated Current	150 A
Number of poles	2
Poles description	2P
Breaking capacity	50 kA 500 V DC 20 kA 250 V DC 125 kA 240 V AC 100 kA 480 V AC 50 kA 600 V AC
System Voltage	500 V DC 600 V AC
Continuous current rating	80 %
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 4...AWG 4/0 aluminium/copper
Phase connection	BA
Magnetic hold current	750 A
Magnetic tripping current	1500 A
Height	11.48 in
Width	4.48 in
Depth	5.87 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product certifications	CCC CE CSA IEC UL listed
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	01122 - HL, JL I-LINE BREAKER/SWITCH
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	4.5
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------