





Circuit breaker

Circuit breaker, PowerPacT J, 200A, 3 pole, 600VAC, 50kA, lugs, thermal magnetic, 80%, shunt

JLP36200SA

! To be discontinued on: Apr 30, 2024



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 7,803.00 USD

Main

Product Or Component Type

| . roudet er eempenent type | Official Distance |
|--|---|
| Complementary | |
| Line Rated Current | 200 A |
| Number Of Poles | 3P |
| Control Type | Toggle |
| Breaking Capacity Code | L |
| Breaking Capacity | 125 kA 240 V AC 50/60 Hz UL 489 100 kA 480 V AC 50/60 Hz UL 489 50 kA 600 V AC 50/60 Hz UL 489 20 kA 250 V DC UL 489 50 kA 500 V DC UL 489 |
| [Ue] Rated Operational Voltage | 600 V AC 50/60 Hz IEC 60947-3 |
| Network Frequency | 50/60 Hz |
| [Ics] Rated Service Breaking Capacity | 125 kA 220/240 V AC 50/60 Hz IEC 60947-2 100 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 50 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2 |
| [Uimp] Rated Impulse Withstand Voltage | 8 kV IEC 60947-2 |
| Trip Unit Technology | Thermal-magnetic |
| Magnetic Tripping Current | 2000 A |
| Magnetic Hold Current | 1000 A |
| Continuous Current Rating | 80 % |
| [Ui] Rated Insulation Voltage | 750 V IEC 60947-2 |
| Protection Type | Overload protection Short-circuit protection |
| Accessory / Separate Part Type | Shunt trip 110130 V AC compartment |
| Suitability For Isolation | Yes IEC 60947-2 |
| Utilisation Category | Category A |
| Awg Gauge | AWG 3/0350 kcmil aluminium/copper terminals |
| Local Signalling | Switched off (OFF) 1 trip indicator green) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Mounting Mode | Unit mount lug) |
|------------------------------------|--|
| Mounting Support | Lug |
| Electrical Connection | Terminal nut, line Lugs, load |
| Terminal Identifier | AL250JD |
| Long Time Pick-Up Adjustment Range | 0.251 x ln |
| Tightening Torque | 221.27 lbf.in (25 N.m) 0.150.29 in² (95185 mm²) (AWG 3/0350 kcmil) |
| Number Of Slots | 2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in) |
| Power Wire Stripping Length | 0.98 in (25 mm) |
| Height | 7.52 in (191 mm) |
| Width | 4.09 in (104 mm) |
| Depth | 3.39 in (86 mm) |
| Net Weight | 5.29 lb(US) (2.4 kg) |
| Communication Interface | Modbus |
| Circuit Breaker Application | HACR rated |

Environment

| Quality Labels | CE |
|---------------------------------------|---|
| Standards | UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2 |
| Product Certifications | UL CSA NOM |
| Ip Degree Of Protection | Front cover IP40 |
| Pollution Degree | 3 |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Ambient Air Temperature For Storage | -58185 °F (-5085 °C) |
| Operating Altitude | < 6561.68 ft (2000 m) without derating 5000 m with derating |

Ordering and shipping details

| Category | US10DE201120 | |
|-------------------|--------------|--|
| Discount Schedule | 0DE2 | |
| Returnability | No | |
| Country Of Origin | US | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.13 in (13.018 cm) |

| Package 1 Width | 7.25 in (18.415 cm) |
|------------------|------------------------|
| Package 1 Length | 8.44 in (21.433 cm) |
| Package 1 Weight | 5.00 lb(US) (2.268 kg) |

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free | |
|----------|----------------------------|-----|
| ② | Rohs Exemption Information | Yes |
| ⊘ | Pvc Free | |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |