

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Circuit breaker
Range of product	PowerPact J
Trip unit technology	Thermal-magnetic
Breaking capacity code	R

Complementary

Line Rated Current	225 A
Number of poles	3
Poles description	3P
Breaking capacity	200 kA 240 V AC 200 kA 480 V AC 100 kA 600 V AC
System Voltage	600 V AC
Continuous current rating	80 %
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 3/0...350 kcmil aluminium/copper
Phase connection	ABC
Magnetic hold current	1125 A
Magnetic tripping current	2250 A
Height	11.48 in
Width	4.48 in
Depth	5.87 in

Environment

Product certifications	CCC CE
------------------------	-----------

CSA
IEC
UL listed

Ambient air temperature for operation 104 °F (40 °C)

Ordering and shipping details

Category	01109 - H/J HIGH INTERRUPT I-LINE CB/SW
Discount Schedule	DE2
GTIN	00785901256861
Nbr. of units in pkg.	1
Package weight(Lbs)	6.8500000000000005
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0832 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov