

# LA36125

## 3P 125A, 600V, LA FA/LA MOLDED CASE CIRCUIT BREAKER

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 4,944.00 USD



### Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip Unit Type	Thermal-magnetic
Rating Code	A

### Complementary

Line Rated Current	125 A
Number of Poles	3P
Interrupt Rating	42 kA 120 V AC 42 kA 240 V AC 30 kA 480Y/277 V AC 30 kA 480 V AC 10 kA 125 V DC
[Ue] rated operational voltage	600 V AC 250 V DC
Mounting mode	I-Line
Electrical connection	Lugs load I-Line connection line
Wire Gauge	AWG 1...600 kcmil aluminium/copper)1 AWG 1...250 kcmil aluminium/copper)2
Terminal Type	AL400LA
Magnetic hold current	625 A
Magnetic tripping current	1250 A
Wiring configuration	3-wire
Height	279.40 mm (11 in)
Width	152.40 mm (6 in)
Depth	148.34 mm (5.84 in)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Product certifications	CSA UL listed
------------------------	------------------

## Ordering and shipping details

Category	01040 - LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901339267
Package weight(Lbs)	8.20 kg (18.08 lb(US))
Returnability	Yes
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DIDP and DINP which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------