



### Main

|                                    |                      |
|------------------------------------|----------------------|
| Range                              | TeSys                |
| Product or component type          | Terminal block       |
| Device short name                  | LA7K                 |
| Accessory / separate part category | Connection accessory |
| Mounting support                   | Rail                 |
| Product compatibility              | LR2K<br>LR7K         |

### Complementary

|                         |  |
|-------------------------|--|
| Connections - terminals | Screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> ) - cable stiffness: solid<br>Screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (0.75...4 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end<br>Screw clamp terminals 1 cable(s) 0...0 in <sup>2</sup> (0.34...2.5 mm <sup>2</sup> ) - cable stiffness: flexible - with cable end<br>Screw clamp terminals 2 cable(s) 0...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> ) - cable stiffness: solid<br>Screw clamp terminals 2 cable(s) 0...0.01 in <sup>2</sup> (0.75...4 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end<br>Screw clamp terminals 2 cable(s) 0...0 in <sup>2</sup> (0.34...1.5 mm <sup>2</sup> ) - cable stiffness: flexible - with cable end |
| Tightening torque       | 0.8 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>0.8 N.m - on screw clamp terminals - with screwdriver Philips No 2  |
| Height                  | 3.15 in (80 mm)  |
| Width                   | 1.77 in (45 mm)  |
| Depth                   | 2.95 in (75 mm)  |
| Product weight          | 0.22 lb(US) (0.1 kg)   |
| Quantity per set        | Set of 10  |

### Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 22341 - CONTACTOR,D,K,&F ACCESS |
| Discount Schedule     | I12                             |
| GTIN                  | 00785901913597                  |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 0.11                            |
| Returnability         | Y                               |

|                   |    |
|-------------------|----|
| Country of origin | CZ |
|-------------------|----|

**Offer Sustainability**

|                           |   |
|---------------------------|---|
| RoHS (date code: YYWW)    | Compliant - since 0849 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                     | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| California proposition 65 | WARNING: This product can expose you to chemicals including:  |
| ----- Substance 1         | Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.  |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>   |

**Contractual warranty**

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|