

Product data sheet

Specifications



Fuse disconnecter, TeSys DF, 1P, 600V, 30A, 10 x 38mm, Add on for LS1D32

LA8D324

 **Discontinued on:** Oct 22, 2020

 **Discontinued**

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys
Product Or Component Type	Fuse-disconnector
Device Short Name	LA8D
Poles Description	1P

Complementary

Mounting Support	Rail
Mounting Position	Vertical +/- 23°
Control Type	Toggle
[Ue] Rated Operational Voltage	600 V
[Ie] Rated Operational Current	30 A
Local Signalling	Blown fuse indication
Fuse Size	10 x 38 mm
Fuse Type	AM GG
Associated Fuse Rating	30 A aM 30 A gG
Connections - Terminals	screw clamp terminals 2 0.00...0.01 in ² (1...6 mm ²)solid screw clamp terminals 2 0.00...0.01 in ² (1...6 mm ²)flexible without cable end screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²)flexible with cable end
Tightening Torque	15.05 lbf.in (1.7 N.m) screw clamp terminals

Environment

Standards	IEC 60947-2 IEC 60947-1 IEC 60947-4-1
Product Certifications	BV
Protective Treatment	TH
Ambient Air Temperature For Operation	-58...158 °F (-50...70 °C) operation
Height	3.50 in (89 mm)
Width	1.77 in (45 mm)
Depth	2.69 in (68.3 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0I12
Gtin	00785901046950
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	2.26 oz (64.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	20
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.45 lb(US) (1.567 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	560
Package 3 Height	30.31 in (77.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	23.62 in (60.0 cm)
Package 3 Weight	96.52 lb(US) (43.78 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	