

LAD5C12

TeSys - connection module - for reversing motor starter - 9...32 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 16.20 USD



Main

Range of product	TeSys
Device short name	LAD5C
Product or component type	Connection module
Accessory / separate part category	Connection accessory
Function	Connection to PLC I/O module
[Uc] control circuit voltage	24 V DC

Complementary

Mounting location	Front
Connector type	RJ45
Monitoring and control	Modicon STB Modicon Telefast Modicon TM3
Product compatibility	GV2P LC2D LC1D GV2DM GV2ME
Motor starter type	Reversing
Power rated current	9...32 A on AC-3
Starter control terminal	Screw clamp terminals
Product certifications	CE CUL
Height	8.03 in (204 mm)
Width	3.54 in (90 mm)
Depth	1.5 in (38 mm)
Product weight	2.36 oz (67 g)
Quantity per set	3

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901946694
Nbr. of units in pkg.	3
Package weight(Lbs)	0.28000000000000003
Returnability	N
Country of origin	LV

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations