



Price** : 20.70 USD



Main

Range of product	TeSys D TeSys D control relay TeSys F
Range	TeSys
Product or component type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NC
Connections - terminals	lugs-ring terminals

Complementary

Mounting location	Front
[Ui] rated insulation voltage	600 V UL 690 V IEC 60947-5-1 600 V CSA
[Ue] rated operational voltage	690 V AC 25...400 Hz
[Ith] conventional free air thermal current	10 A 140 °F (60 °C)
Irms rated making capacity	140 A AC 250 A DC
Permissible short-time rating	100 A 140 °F (60 °C) 1 s 120 A 140 °F (60 °C) 500 ms 140 A 140 °F (60 °C) 100 ms
Protection type	GG fuse 10 A rating according to operational current for Ue <= 690 V
Associated fuse rating	10 A gG IEC 60947-5-1
Mechanical durability	30 Mcycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non-overlap time	1.5 ms on de-energisation no overlap between NC and NO contact

1.5 ms on energisation no overlap between NC and NO contact

Overlap time	1.5 ms
Insulation resistance	> 10 MOhm

Environment

Environmental characteristic	Normal environment
Standards	NF C 63-140 EN 60947-5-1 IEC 60947-5-1 VDE 0660 BS 4794
Product certifications	CSA UL
IP degree of protection	IP2x VDE 0106
Protective treatment	TH IEC 60068
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	03389110820775
Package weight(Lbs)	0.03 kg (0.07 lb(US))
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: No which is known to the State of California to cause No harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------