

# LAL26400WB8041

## FA/LA MOLDED CASE CIRCUIT BREAKER 600V, 400A, 2P, MECH INTERLOCK, WIRE TERMINAL

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 4,815.00 USD



### Main

Product or component type	Circuit breaker
Trip Unit Type	Thermal-magnetic
Options	Control wire Mechanical interlock

### Complementary

Line Rated Current	400 A
Number of Poles	2P
Interrupt Rating	42 kA at 240 V AC 30 kA at 480 V AC 22 kA at 600 V AC 10 kA at 125 V DC 10 kA at 250 V DC
System Voltage	250 V DC 600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
Wire Gauge	AWG 1...600 kcmil (aluminium/copper) 1 cable(s) AWG 1...250 kcmil (aluminium/copper) 2 cable(s)
Terminal Type	AL400LA
Magnetic hold current	2000 A
Magnetic tripping current	4000 A
Height	11 in
Width	6 in
Depth	5.84 in

## Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

## Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901560890
Nbr. of units in pkg.	1
Package weight(Lbs)	14.18
Returnability	N
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1304 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------