

Product data sheet

Characteristics

LAL363001021

FA/LA MOLDED CASE CIRCUIT BREAKER, 600VAC/250VDC, 300A, 3P, SHUNT TRIP

Product availability : Stock - Normally stocked in distribution facility



Price* : 5,525.00 USD



Main

Product or component type	Circuit breaker
Trip Unit Type	Thermal-magnetic
Options	Shunt trip 120/208/240 V AC

Complementary

Line Rated Current	300 A
Number of Poles	3P
Interrupt Rating	42 kA at 240 V AC 30 kA at 480 V AC 22 kA at 600 V AC 10 kA at 125 V DC 10 kA at 250 V DC
System Voltage	250 V DC 600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load Lugs line
Wire Gauge	AWG 1...600 kcmil (aluminium/copper) 1 cable(s) AWG 1...250 kcmil (aluminium/copper) 2 cable(s)
Terminal Type	AL400LA
Magnetic hold current	1500 A
Magnetic tripping current	3000 A
Height	11 in
Width	6 in
Depth	5.84 in

Environment

Product certifications	CSA
------------------------	-----

Feb 23, 2019

IEC
UL listed

Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901339472
Nbr. of units in pkg.	1
Package weight(Lbs)	16.77
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1304 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------