

# Product data sheet

## Characteristics

# LAL364001590

## FA/LA MOLDED CASE CIRCUIT BREAKER 600V, 400A, 3P,AUX SWITCH,UNDERVOLTAGE RELEASE

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 5,900.00 USD



### Main

Product or component type	Circuit breaker
Trip Unit Type	Thermal-magnetic
Options	Auxiliary switch 1 NO + 1 NC

### Complementary

Line Rated Current	400 A
Number of Poles	3P
Interrupt Rating	42 kA at 240 V AC
System Voltage	600 V AC
Mounting mode	Unit mount
Electrical connection	Lugs load
Wire Gauge	AWG 1...600 kcmil (aluminium/copper) 1 cable(s)
Terminal Type	AL400LA
Magnetic hold current	2000 A
Magnetic tripping current	4000 A
Height	11 in
Width	6 in
Depth	5.84 in

### Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901844082
Nbr. of units in pkg.	1
Package weight(Lbs)	16.77
Returnability	N
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1304 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------