

Product data sheet

Characteristics

LB1LD03M57

TeSys integral - protection module - AC-43 - thermal-magnetic - 35...50 A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 269.00 USD



Main

Range	TeSys
Device short name	LB1LD
Product or component type	Protection module
Range compatibility	TeSys Integral contactor breaker
Poles description	3P
Utilisation category	AC-43
System Voltage	690 V AC
Thermal protection adjustment range	35...50 A
Magnetic tripping current	300...600 A
Trip unit technology	Thermal-magnetic
Protection type	Phase imbalance
Thermal overload class	Class 20

Complementary

Motor power kW	11 kW at 220...240 V AC 50/60 Hz 25 kW at 400...415 V AC 50/60 Hz 25 kW at 440 V AC 50/60 Hz 33 kW at 480...525 V AC 50/60 Hz 45 kW at 600...690 V AC 50/60 Hz
Product weight	1.72 lb(US) (0.78 kg)

Environment

Standards	NF C 63-650
Protective treatment	TH
IP degree of protection	IP20 B conforming to IEC 60144 IP20 B conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C)

Ordering and shipping details

Category	22384 - STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	00785901257431
Nbr. of units in pkg.	1
Package weight(Lbs)	2.3399999999999999
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------