

# LGP36400U31X

## PowerPact L Circuit Breaker, Micrologic3.3, 400A, 3P, 600V, 18kA

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 5,081.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact L
Trip Unit Type	Electronic, standard, Micrologic 3.3, LI
Interrupt Code	G

### Complementary

Protection technology	Current limiter
Line Rated Current	400 A
Number of Poles	3P
Interrupt Rating	18 kA 600 V AC 35 kA 480 V AC 65 kA 240 V AC
Voltage Rating	600 V AC
Continuous current rating	80 %
Mounting mode	Unit mount
Electrical connection	Terminal nut line Lugs load
Wire Size	AWG 2/0...500 kcmil aluminium/copper)2
Terminal Type	AL600LS52K3
Height	287.02 mm (11.3 in)
Width	139.70 mm (5.5 in)
Depth	167.89 mm (6.61 in)
Tightening torque	38.94...442.54 lbf.in (4.4...50 N.m) 0.11...0.37 in <sup>2</sup> (70...240 mm <sup>2</sup> ) AWG 2/0...500 kcmil)

### Environment

Product certifications	CE UL listed
------------------------	-----------------

CCC  
IEC  
NMX  
CSA

### Ordering and shipping details

Category	01116 - L ELEC TRIP UNIT MOUNT BREAKER/SW
Discount Schedule	DE2
GTIN	00785901639824
Package weight(Lbs)	6.80 kg (15 lb(US))
Returnability	Yes
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------