

LH36350

LH MOLDED CASE CIRCUIT BREAKER, 600V, 350A, 3P

Product availability : Stock - Normally stocked in distribution facility



Price** : 8,145.00 USD



Main

Product or component type	Circuit breaker
Range of product	I-Line
Trip Unit Type	Thermal-magnetic
Rating Code	H

Complementary

Line Rated Current	350 A
Number of Poles	3P
Interrupt Rating	65 kA at 240 V AC 35 kA at 480 V AC 25 kA at 600 V AC
System Voltage	250 V DC 600 V AC
Mounting mode	I-Line
Electrical connection	I-Line connection line Lugs load
Wire Gauge	AWG 1...600 kcmil (aluminium/copper) 1 cable(s) AWG 1...250 kcmil (aluminium/copper) 2 cable(s)
Terminal Type	AL400LA
Magnetic hold current	1750 A
Magnetic tripping current	3500 A
Height	12.5 in
Width	6 in
Depth	4 in

Environment

Product certifications	CSA
------------------------	-----

Ordering and shipping details

Category	01040 - LA/LH BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901339427
Nbr. of units in pkg.	1
Package weight(Lbs)	18.280000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1304 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------