



Price** : 10,541.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact L
Trip Unit Type	Electronic, standard, Micrologic 3.3, LI
Interrupt Code	J

Complementary

Protection technology	Current limiter
Line Rated Current	600 A
Number of Poles	3P
Interrupt Rating	65 kA 480 V AC 100 kA 240 V AC 25 kA 600 V AC
Voltage Rating	600 V AC
Continuous current rating	80 %
Mounting mode	Unit mount
Electrical connection	Busbar connection line Busbar connection load
Terminal Type	AL600LF52K3
Height	287.02 mm (11.3 in)
Width	139.70 mm (5.5 in)
Depth	167.89 mm (6.61 in)
Tightening torque	38.94...442.54 lbf.in (4.4...50 N.m) 0.15...0.37 in ² (95...240 mm ²) AWG 3/0...500 kcmil)

Environment

Product certifications	CCC CE CSA UL listed
------------------------	-------------------------------

Ordering and shipping details

Category	01116-L ELEC TRIP UNIT MOUNT BREAKER/SW
Discount Schedule	DE2
GTIN	00785901474906
Package weight(Lbs)	15.00 lb(US) (6.804 kg)
Returnability	Yes
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------