# **Product data sheet**

Specifications





# Electric motor MCH, MasterPact MTZ1 drawout, remote operation, 24/30VDC

LV847460

#### Main

| Range                     | MasterPact                 |
|---------------------------|----------------------------|
| Device Short Name         | мсн                        |
| Product Or Component Type | Motor mechanism            |
| Device Application        | Control                    |
| Range Compatibility       | Masterpact MasterPact MTZ1 |

## Complementary

| Control Type                    | Standard                        |
|---------------------------------|---------------------------------|
| Mounting Mode                   | Drawout                         |
| [Uc] Control Circuit Voltage    | 2430 V DC                       |
| Threshold Tripping Voltage      | 0.851.1 Un                      |
| Maximum Power Consumption In Va | 180 VA                          |
| Overcurrent Protection          | 23 x ln 0.1 s                   |
| Maximum Charging Time           | 3 s                             |
| Maximum Operating Frequency     | <= 3 cycles per minute          |
| Provided Contact                | Limit switch contact 240 V 10 A |

## Ordering and shipping details

Gtin 3606480811920

## **Packing Units**

| Unit Type Of Package 1       | PCE                    |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 2.56 in (6.5 cm)       |
| Package 1 Width              | 5.12 in (13.0 cm)      |
| Package 1 Length             | 7.09 in (18.0 cm)      |
| Package 1 Weight             | 2.26 lb(US) (1.024 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration  |
|---------------------------|--|
| Eu Rohs Directive         | Compliant with Exemptions  |
| China Rohs Regulation     | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.   |
| Environmental Disclosure  | Product Environmental Profile  |
| Circularity Profile       | End of Life Information  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |