Product data sheet





Switch disconnector, MasterPact MTZ2 25HF, 2500A, 187kA/ 690VAC 50/60Hz (Icm), 3P, fixed

LV848075

Main

Range	MasterPact
Product Or Component Type	Switch disconnector
Device Application	Distribution
Switch-Disconnector Name	MasterPact MTZ2 25 HF
Poles Description	3P
Network Type	AC
Network Frequency	50/60 Hz

Complementary

Control Type	Push-button
Mounting Mode	Fixed
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz EN/IEC 60947-3
[le] Rated Operational Current	2500 A AC 50/60 Hz 690 V
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz EN/IEC 60947-3
[Uimp] Rated Impulse Withstand Voltage	12 kVEN/IEC 60947-3
[Icw] Rated Short-Time Withstand Current	85 kA 1 s EN/IEC 60947-3 75 kA 3 s EN/IEC 60947-3
[Icm] Rated Short-Circuit Making Capacity	187 kA peak 220690 V AC 50/60 Hz
Utilisation Category	AC-23A AC-3
Performance Level	HF
Suitability For Isolation	Yes EN/IEC 60947-3
Contact Position Indicator	Yes
Visible Break	No
Mechanical Durability	20000 cycles with periodic preventive maintenance EN/IEC 60947-3
Electrical Durability	AC-23A 5000 cycles 440 V AC 50/60 Hz EN/IEC 60947-3 AC-23A 2500 cycles 690 V AC 50/60 Hz EN/IEC 60947-3
Connection Pitch	4.53 in (115 mm)
Height	13.86 in (352 mm)
Width	16.61 in (422 mm)
Depth	11.81 in (300 mm)

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.



Net Weight	110.23 lb(US) (50 kg)
Standards	EN/IEC 60947-3
Product Certifications	IECEE CB Scheme
Ip Degree Of Protection	IP30
Pollution Degree	3 EN/IEC 60947-4-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

Ordering and shipping details

Gtin 3606480817441

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.86 in (35.2 cm)
Package 1 Width	16.61 in (42.2 cm)
Package 1 Length	11.81 in (30.0 cm)
Package 1 Weight	110.23 lb(US) (50.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov